

# VS-PPC-C1-PC-ROBK-L - Protective cover



1405293

<https://www.phoenixcontact.com/us/products/1405293>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Protective cover, degree of protection: IP65/IP67, color: black



Snap-on cap

## Your advantages

- Compatible with IP67 panel-mount frame
- Safe operation with the right degree of protection
- Robust industrial design

## Commercial data

Item number	1405293
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOBZ
GTIN	4046356420402
Weight per piece (including packing)	8.1 g
Weight per piece (excluding packing)	2.497 g
Customs tariff number	39269097
Country of origin	DE

1405293

<https://www.phoenixcontact.com/us/products/1405293>

## Technical data

### Product properties

Product type	Protective cover
Type	Version 14

### Dimensions

Width	20 mm
Height	22.6 mm
Length	20.9 mm

### Material specifications

Color	black
Material	Plastic
Flammability rating according to UL 94	V0
Seal material	NBR

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 55 °C

# VS-PPC-C1-PC-ROBK-L - Protective cover



1405293

<https://www.phoenixcontact.com/us/products/1405293>

## Classifications

### ECLASS

ECLASS-13.0	27440208
ECLASS-15.0	27440208

### ETIM

ETIM 10.0	EC002314
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VS-PPC-C1-PC-ROBK-L - Protective cover



1405293

<https://www.phoenixcontact.com/us/products/1405293>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)