

# VS-04-C-SDB/PH/0,3 - USB cable



1405565

<https://www.phoenixcontact.com/us/products/1405565>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

USB cable, with USB connectors at one end, assembled connector type: B, single post connector, length: 0.3 m



## Commercial data

Item number	1405565
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB14
Product key	ABNDBA
GTIN	4046356460583
Weight per piece (including packing)	20 g
Weight per piece (excluding packing)	16.1 g
Customs tariff number	85444290
Country of origin	DE

1405565

<https://www.phoenixcontact.com/us/products/1405565>

## Technical data

### Product properties

Product type	Data cable preassembled
Number of positions	4

### Interfaces

Signal type/category	USB 2.0, 480 Mbps
----------------------	-------------------

### Electrical properties

Transmission medium	Copper
Transmission speed	480 Mbps
Transmission characteristics (category)	USB 2.0
Transmission speed	480 Mbps

### Material specifications

Outer sheath, material	PVC
------------------------	-----

### Connector

#### Connection 1

Type	Plug straight USB type B
------	--------------------------

#### Connection 2

Type	Individual pin plug
------	---------------------

### Cable/line

Cable structure	2xAWG28 + 2xAWG24
Signal type/category	USB 2.0, 480 Mbps
Outer sheath, material	PVC
External sheath, color	gray

# VS-04-C-SDB/PH/0,3 - USB cable



1405565

<https://www.phoenixcontact.com/us/products/1405565>

## Classifications

### ECLASS

ECLASS-13.0	27060308
ECLASS-15.0	27060328

### ETIM

ETIM 9.0	EC001262
----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# VS-04-C-SDB/PH/0,3 - USB cable



1405565

<https://www.phoenixcontact.com/us/products/1405565>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)