

HC-B06-SP-RBK - Profile gasket



1407706

<https://www.phoenixcontact.com/us/products/1407706>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Profile gasket for HEAVYCON EVO supporting base element type B6



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1407706 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BF66 |
| Product key | AF7AUX |
| GTIN | 4046356778008 |
| Weight per piece (including packing) | 2.64 g |
| Weight per piece (excluding packing) | 2.7 g |
| Customs tariff number | 40169300 |
| Country of origin | IT |

HC-B06-SP-RBK - Profile gasket



1407706

<https://www.phoenixcontact.com/us/products/1407706>

Technical data

Product properties

| | |
|--------------|------------------------|
| Product type | Seal |
| Application | for base housing (EVO) |

Material specifications

| | |
|------------------------------|-----|
| Seal material Profile gasket | NBR |
|------------------------------|-----|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

Mounting

| | |
|---------------|--|
| Assembly note | The replacement seal should be bonded with Loctite 454 adhesive. |
| | For HC-EVO-B06...BK housing |


HC-B06-SP-RBK - Profile gasket

1407706

<https://www.phoenixcontact.com/us/products/1407706>



Drawings



Dimensional drawing

HC-B06-SP-RBK - Profile gasket



1407706

<https://www.phoenixcontact.com/us/products/1407706>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1407706>



EAC

Approval ID: RU C-DE.AI30.B.01102

HC-B06-SP-RBK - Profile gasket



1407706

<https://www.phoenixcontact.com/us/products/1407706>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 23071590 |
| ECLASS-15.0 | 27440292 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002943 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31401600 |
|-------------|----------|

HC-B06-SP-RBK - Profile gasket



1407706

<https://www.phoenixcontact.com/us/products/1407706>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.111 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com