

# CUC-PP-FRAME-19 BK - 19" mounting frame



1409140

<https://www.phoenixcontact.com/us/products/1409140>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

19" frame, empty modular distribution panel, for using 8 modules (6 x RJ45 each) with 48 connections in total, 1 HE, color similar to RAL 9005



19" mounting frame (black)

## Product description

19" frame, empty, for using 8 modules (6x RJ45 each) with 48 connections in total, 1 RU, color similar to RAL 9005

## Commercial data

Item number	1409140
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	ABNMAY
GTIN	4046356862462
Weight per piece (including packing)	1,532 g
Weight per piece (excluding packing)	1,532 g
Customs tariff number	85389099
Country of origin	DE

# CUC-PP-FRAME-19 BK - 19" mounting frame



1409140

<https://www.phoenixcontact.com/us/products/1409140>

## Technical data

### Product properties

Number of slots	8
-----------------	---

### Connection data

Connection method	Screw connection (in connection with the base element)
-------------------	--

### Dimensions

Width	482.6 mm
Height	44.45 mm
Depth	184 mm
Drill hole distance, horizontal	31.6 mm

### Material specifications

Material	Steel, galvanized
Flammability rating according to UL 94	V0
Housing material	Steel, powder-coated
Housing surface material	Powder-coated, black

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-10 °C ... 60 °C

# CUC-PP-FRAME-19 BK - 19" mounting frame



1409140

<https://www.phoenixcontact.com/us/products/1409140>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)