

CUC-PP-PATCHBAY-MH - Marshalling panel



1409283

<https://www.phoenixcontact.com/us/products/1409283>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marshalling panel, design: 19" rack/fix housing, degree of protection: IP20, material: Steel, powder-coated, connection method: Screw connection, housing size: 1, color: light gray RAL 7035



Jumpering panel, 19" (gray, with 5 metal brackets)

Product description

Marshalling distributor panel, 19", 1 RU, with 5 metal brackets

Your advantages

- Robust design
- For easy cable management

Commercial data

Item number	1409283
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB18
Product key	ABNLBZ
GTIN	4046356867078
Weight per piece (including packing)	822.9 g
Weight per piece (excluding packing)	804.63 g
Customs tariff number	94039910
Country of origin	CN

CUC-PP-PATCHBAY-MH - Marshalling panel



1409283

<https://www.phoenixcontact.com/us/products/1409283>

Technical data

Product properties

Product type	Data plug
Type	1RU

Connection data

Connection method	Screw connection
-------------------	------------------

Dimensions

Width	482.6 mm
Height	44.45 mm
Drill hole distance, horizontal	31.6 mm

Material specifications

Color	light gray RAL 7035
Material	Steel, galvanized
Flammability rating according to UL 94	V0
Housing material	Steel, powder-coated
Housing surface material	Powder-coated, gray

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-10 °C ... 60 °C

Mounting

Mounting type	19" rack
---------------	----------

CUC-PP-PATCHBAY-MH - Marshalling panel



1409283

<https://www.phoenixcontact.com/us/products/1409283>

Classifications

ECLASS

ECLASS-13.0	19170192
ECLASS-15.0	19170192

ETIM

ETIM 10.0	EC003626
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-PP-PATCHBAY-MH - Marshalling panel



1409283

<https://www.phoenixcontact.com/us/products/1409283>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com