

SAC-4P-100,0-BF145 - Cable reel



1410758

<https://www.phoenixcontact.com/us/products/1410758>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Cable reel, POC halogen-free, black RAL 9005, 4-wire, color single wire: black 1, black 2, black 3, black 4, irradiated

Commercial data

Item number	1410758
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	AF1LAA
GTIN	4046356906852
Weight per piece (including packing)	7,620 g
Weight per piece (excluding packing)	7,620 g
Country of origin	DE

SAC-4P-100,0-BF145 - Cable reel



1410758

<https://www.phoenixcontact.com/us/products/1410758>

Technical data

Product properties

Product type	Cable by the meter
Number of positions	4

Electrical properties

Nominal voltage U_N	250 V AC
	250 V DC

Cable/line

POC irradiated halogen-free black [BF 145]

Cable weight	75 kg/km
Number of positions	4
Shielded	no
Cable type	POC irradiated halogen-free black [BF 145]
AWG signal line	18
Conductor cross-section	4x 0.75 mm ²
Wire diameter incl. insulation	2.2 mm
External cable diameter	6.90 mm
Outer sheath, material	POC
External sheath, color	black RAL 9005
Conductor material	Tin-plated Cu litz wires
Material wire insulation	POC
Single wire, color	black 1, black 2, black 3, black 4
Overall twist	4 wires around filler to the core
Nominal voltage, cable	300 V
Test voltage	3500 V
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Smallest bending radius, fixed installation	28 mm
Smallest bending radius, movable installation	56 mm
Halogen-free	according to IEC 60754-1
	in accordance with EN 50267-2-1
Flame resistance	according to IEC 60332-1
	in accordance with EN 50265-2-1
Concentration of fumes	in accordance with IEC 61034
	EN 50268-2
Special properties	Irradiated
Ambient temperature (operation)	-55 °C ... 145 °C (cable, fixed installation)
	-35 °C ... 120 °C (Cable, flexible installation)

SAC-4P-100,0-BF145 - Cable reel



1410758

<https://www.phoenixcontact.com/us/products/1410758>

Classifications

ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-4P-100,0-BF145 - Cable reel



1410758

<https://www.phoenixcontact.com/us/products/1410758>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com