

# A-INL-NPT1-P-GY - Counter nut



1411235

<https://www.phoenixcontact.com/us/products/1411235>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads 1"-NPT, color: silver-gray RAL 7001



## Commercial data

Item number	1411235
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	BF68
Product key	AF7DZX
GTIN	4046356923668
Weight per piece (including packing)	6.54 g
Weight per piece (excluding packing)	6.54 g
Customs tariff number	39269097
Country of origin	TR

# A-INL-NPT1-P-GY - Counter nut

1411235


<https://www.phoenixcontact.com/us/products/1411235>

## Technical data

### Product properties

Product type	Flat nut
Thread type	1"-NPT

### Dimensions

Dimensional drawing	
Length	6 mm
Diameter Connecting thread	32.4 mm
Connecting thread diameter	32.4 mm
Wrench size, counter nut	47 mm
Hexagon angular dimension	46.5 mm
Thread type connection side	1"-NPT

### Material specifications

Color	silver gray (RAL 7001)
Material	PA
Flammability rating according to UL 94	V2

### Cable/line

Halogen-free	yes
--------------	-----

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

# A-INL-NPT1-P-GY - Counter nut


1411235

<https://www.phoenixcontact.com/us/products/1411235>



## Drawings

Dimensional drawing



Dimensional drawing

# A-INL-NPT1-P-GY - Counter nut



1411235

<https://www.phoenixcontact.com/us/products/1411235>

## Classifications

### ECLASS

ECLASS-13.0	27140807
ECLASS-15.0	27140807

### ETIM

ETIM 10.0	EC003608
-----------	----------

### UNSPSC

UNSPSC 21.0	31161700
-------------	----------

# A-INL-NPT1-P-GY - Counter nut



1411235

<https://www.phoenixcontact.com/us/products/1411235>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)