

# A-INL-M63-S-S - Counter nut

1411254

<https://www.phoenixcontact.com/us/products/1411254>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads M63 x 1.5, color: silver-colored



## Commercial data

Item number	1411254
Packing unit	1 pc
Minimum order quantity	100 pc
Sales key	BF68
Product key	AF7DZX
GTIN	4046356923873
Weight per piece (including packing)	54 g
Weight per piece (excluding packing)	55 g
Customs tariff number	73181639
Country of origin	DE

# A-INL-M63-S-S - Counter nut

1411254


<https://www.phoenixcontact.com/us/products/1411254>

## Technical data

### Product properties

Product type	Flat nut
Thread type	M63

### Dimensions

Dimensional drawing	
Length	6 mm
Diameter	63 mm
Connecting thread diameter	63 mm
Wrench size, counter nut	70 mm
Hexagon angular dimension	75 mm
Thread type connection side	M63 x 1.5
Thread pitch	1.5 mm

### Material specifications

Material	Stainless steel 1.4305
----------	------------------------

### Cable/line

Halogen-free	yes
--------------	-----

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-70 °C ... 220 °C
---------------------------------	-------------------

# A-INL-M63-S-S - Counter nut


1411254

<https://www.phoenixcontact.com/us/products/1411254>



## Drawings

Dimensional drawing



Dimensional drawing

# A-INL-M63-S-S - Counter nut



1411254

<https://www.phoenixcontact.com/us/products/1411254>

## Classifications

### ECLASS

ECLASS-13.0	27140807
ECLASS-15.0	27140807

### ETIM

ETIM 10.0	EC003608
-----------	----------

### UNSPSC

UNSPSC 21.0	31161700
-------------	----------

# A-INL-M63-S-S - Counter nut



1411254

<https://www.phoenixcontact.com/us/products/1411254>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)