

# A-INL-PG42-N-S - Counter nut

1411265

<https://www.phoenixcontact.com/us/products/1411265>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads Pg42, color: silver-colored



## Commercial data

Item number	1411265
Packing unit	25 pc
Minimum order quantity	100 pc
Sales key	BF68
Product key	AF7DZX
GTIN	4046356923965
Weight per piece (including packing)	33.048 g
Weight per piece (excluding packing)	33.048 g
Customs tariff number	74198090
Country of origin	DE

# A-INL-PG42-N-S - Counter nut

1411265


<https://www.phoenixcontact.com/us/products/1411265>

## Technical data

### Product properties

Product type	Flat nut
Thread type	Pg42

### Dimensions

Dimensional drawing	
Length	5 mm
Diameter Connecting thread	54 mm
Connecting thread diameter	54 mm
Wrench size, counter nut	60 mm
Hexagon angular dimension	65 mm
Thread type connection side	Pg42

### Material specifications

Material	Brass, nickel-plated
----------	----------------------

### Cable/line

Halogen-free	yes
--------------	-----

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-70 °C ... 220 °C
---------------------------------	-------------------

# A-INL-PG42-N-S - Counter nut


1411265

<https://www.phoenixcontact.com/us/products/1411265>



## Drawings

Dimensional drawing



# A-INL-PG42-N-S - Counter nut



1411265

<https://www.phoenixcontact.com/us/products/1411265>

## Classifications

### ECLASS

ECLASS-13.0	27140807
ECLASS-15.0	27140807

### ETIM

ETIM 10.0	EC003608
-----------	----------

### UNSPSC

UNSPSC 21.0	31161700
-------------	----------

# A-INL-PG42-N-S - Counter nut



1411265

<https://www.phoenixcontact.com/us/products/1411265>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	2b7cac3b-ac0e-4958-9f7b-1d09e27aa79d

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)