

# CUC-V06-F1PGY-UBB/UBAB - Panel mounting frame set



1411905

<https://www.phoenixcontact.com/us/products/1411905>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



USB socket insert, 4-pos., USB socket type A to USB socket type B, socket type B to panel mounting frame side, for the Freenet system in the panel mounting frame, IP20 terminal outlet, 19" patch panel, and service interface

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1411905       |
| Packing unit                         | 5 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AB14          |
| Product key                          | ABNNFC        |
| GTIN                                 | 4046356945004 |
| Weight per piece (including packing) | 18.1 g        |
| Weight per piece (excluding packing) | 14.335 g      |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# CUC-V06-F1PGY-UBB/UBAB - Panel mounting frame set



1411905

<https://www.phoenixcontact.com/us/products/1411905>

## Technical data

### Product properties

|                     |                   |
|---------------------|-------------------|
| Product type        | Panel-mount frame |
| Type                | USB-A             |
| Number of positions | 4                 |
| Connection profile  | USB               |

### Electrical properties

|   |          |
|---|----------|
| Rated voltage (III/3)                   | 30 V     |
| Rated current                           | 1 A      |
| Transmission medium                     | Copper   |
| Transmission speed                      | 480 Mbps |
| Transmission characteristics (category) | USB 2.0  |

### Material specifications

|  |                  |
|--|------------------|
| Color                                  | gray             |
| Material                               | Plastic          |
| Flammability rating according to UL 94 | V0               |
| Housing material                       | Plastic          |
| Cable seal material                    | NBR              |
| Contact material                       | Copper alloy     |
| Contact surface material               | Gold over nickel |
| Contact carrier material               | PC               |
| O-ring material                        | FPM              |

### Mechanical properties

#### Mechanical data

|                             |        |
|-----------------------------|--------|
| Insertion/withdrawal cycles | ≥ 1000 |
|-----------------------------|--------|

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Degree of protection            | IP67             |
| Ambient temperature (operation) | -15 °C ... 65 °C |

# CUC-V06-F1PGY-UBB/UBAB - Panel mounting frame set



1411905

<https://www.phoenixcontact.com/us/products/1411905>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-15.0 | 27440318 |
| ECLASS-13.0 | 27440390 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002597 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# CUC-V06-F1PGY-UBB/UBAB - Panel mounting frame set



1411905

<https://www.phoenixcontact.com/us/products/1411905>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.925 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)