

# HC-D25-SG-RBK - Flat gasket

1414670

<https://www.phoenixcontact.com/us/products/1414670>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Replacement flat gasket, for HEAVYCON EVO panel mounting base HC-EVO-D25.....BK



## Commercial data

Item number	1414670
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF66
Product key	AF7APZ
GTIN	4055626031217
Weight per piece (including packing)	4.71 g
Weight per piece (excluding packing)	4.52 g
Customs tariff number	40169300
Country of origin	DE

# HC-D25-SG-RBK - Flat gasket

1414670


<https://www.phoenixcontact.com/us/products/1414670>

## Technical data

### Product properties

Product type	Seal
Type	D25

### Dimensions

Dimensional drawing	
Width	39.2 mm
Height	2 mm
Length	97 mm
Drill hole distance, horizontal	86 mm
Drill hole distance, vertical	17.5 mm
Hole diameter	7.1 mm

### Material specifications

Seal material Flat gasket	NBR
---------------------------	-----

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

### Mounting

Assembly note	For HC-EVO-D25...BK housing
---------------	-----------------------------

# HC-D25-SG-RBK - Flat gasket


1414670

<https://www.phoenixcontact.com/us/products/1414670>



## Drawings

Dimensional drawing



Dimensional drawing

# HC-D25-SG-RBK - Flat gasket

1414670

<https://www.phoenixcontact.com/us/products/1414670>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1414670>



**EAC**

Approval ID: RU C-DE.AI30.B.01102

# HC-D25-SG-RBK - Flat gasket



1414670

<https://www.phoenixcontact.com/us/products/1414670>

## Classifications

### ECLASS

ECLASS-13.0	23071590
ECLASS-15.0	27440292

### ETIM

ETIM 10.0	EC002943
-----------	----------

### UNSPSC

UNSPSC 21.0	31401600
-------------	----------

# HC-D25-SG-RBK - Flat gasket



1414670

<https://www.phoenixcontact.com/us/products/1414670>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)