

# HC-D15-SP-RBK - Profile gasket



1414671

<https://www.phoenixcontact.com/us/products/1414671>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Replacement profile gasket, for HC-EVO-D15.....BK housing



## Commercial data

Item number	1414671
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF66
Product key	AF7APZ
GTIN	4055626031224
Weight per piece (including packing)	2.6 g
Weight per piece (excluding packing)	2.6 g
Customs tariff number	40169300
Country of origin	IT

# HC-D15-SP-RBK - Profile gasket



1414671


<https://www.phoenixcontact.com/us/products/1414671>

## Technical data

### Product properties

Product type	Seal
Type	D15

### Dimensions

Dimensional drawing	
Width	30 mm
Height	4 mm
Length	63.5 mm

### Material specifications

Seal material Profile gasket	NBR
------------------------------	-----

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

### Mounting

Assembly note	The replacement seal should be bonded with Loctite 454 adhesive.
	For HC-EVO-D15...BK housing


# HC-D15-SP-RBK - Profile gasket

1414671

<https://www.phoenixcontact.com/us/products/1414671>



## Drawings



Dimensional drawing

# HC-D15-SP-RBK - Profile gasket



1414671

<https://www.phoenixcontact.com/us/products/1414671>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1414671>



**EAC**

Approval ID: RU C-DE.AI30.B.01102

# HC-D15-SP-RBK - Profile gasket



1414671

<https://www.phoenixcontact.com/us/products/1414671>

## Classifications

### ECLASS

ECLASS-13.0	23071590
ECLASS-15.0	27440292

### ETIM

ETIM 10.0	EC002943
-----------	----------

### UNSPSC

UNSPSC 21.0	31401600
-------------	----------

# HC-D15-SP-RBK - Profile gasket



1414671

<https://www.phoenixcontact.com/us/products/1414671>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)