

# QPD PSK 5X1,5 - Protective cap

1414759

<https://www.phoenixcontact.com/us/products/1414759>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Protective cap plastic, for 5x 1.5 mm<sup>2</sup> QPD connector, IP50.



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1414759       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BF50          |
| Product key                          | AF6ZBX        |
| GTIN                                 | 4055626033686 |
| Weight per piece (including packing) | 2.5 g         |
| Weight per piece (excluding packing) | 2.54 g        |
| Customs tariff number                | 39269097      |
| Country of origin                    | DE            |

# QPD PSK 5X1,5 - Protective cap



1414759

<https://www.phoenixcontact.com/us/products/1414759>

## Technical data

### Product properties

|                        |                |
|------------------------|----------------|
| Product type           | Protective cap |
| Product family         | QPD            |
| Type                   | QPD            |
| Retaining cord present | no             |
| Seal present           | no             |

### Dimensions

|        |         |
|--------|---------|
| Width  | 21.7 mm |
| Height | 36.5 mm |
| Length | 21.7 mm |

### Material specifications

|                         |         |
|-------------------------|---------|
| Material Protective cap | Plastic |
|-------------------------|---------|

### Environmental and real-life conditions

#### Ambient conditions

|   |                  |
|---|------------------|
| Degree of protection                    | IP50             |
|   | IP50             |
| Ambient temperature (operation)         | -40 °C ... 80 °C |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |

# QPD PSK 5X1,5 - Protective cap

1414759

<https://www.phoenixcontact.com/us/products/1414759>



## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1414759>



**DNV GL**

Approval ID: TAE00003J5

# QPD PSK 5X1,5 - Protective cap



1414759

<https://www.phoenixcontact.com/us/products/1414759>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440208 |
| ECLASS-15.0 | 27440208 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002314 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# QPD PSK 5X1,5 - Protective cap



1414759

<https://www.phoenixcontact.com/us/products/1414759>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)