

A-INL-NPT3/4-N-S - Counter nut



1416011

<https://www.phoenixcontact.com/us/products/1416011>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, shielding: no, for threads 3/4"-NPT, color: silver-colored



Commercial data

Item number	1416011
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	BF68
Product key	AF7DZX
GTIN	4055626056128
Weight per piece (including packing)	21.48 g
Weight per piece (excluding packing)	21.48 g
Customs tariff number	74153300
Country of origin	IN

A-INL-NPT3/4-N-S - Counter nut

1416011


<https://www.phoenixcontact.com/us/products/1416011>

Technical data

Product properties

Product type	Flat nut
Shielded	no
Thread type	3/4"-NPT

Dimensions

Dimensional drawing	
Length	5.5 mm
Diameter	25.9 mm
Connecting thread diameter	25.9 mm
Wrench size, counter nut	32 mm
Hexagon angular dimension	36 mm
Thread type connection side	3/4"-NPT

Material specifications

Material	Brass, nickel-plated
----------	----------------------

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-70 °C ... 220 °C
---------------------------------	-------------------

A-INL-NPT3/4-N-S - Counter nut


1416011

<https://www.phoenixcontact.com/us/products/1416011>



Drawings

Dimensional drawing



Dimensional drawing

A-INL-NPT3/4-N-S - Counter nut



1416011

<https://www.phoenixcontact.com/us/products/1416011>

Classifications

ECLASS

ECLASS-13.0	27140807
ECLASS-15.0	27140807

ETIM

ETIM 10.0	EC003608
-----------	----------

UNSPSC

UNSPSC 21.0	31161700
-------------	----------

A-INL-NPT3/4-N-S - Counter nut



1416011

<https://www.phoenixcontact.com/us/products/1416011>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	bce55fa7-0662-41f4-ae66-035e4fb67098

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com