

# HC-B06-TFL-H-O2STM20S - Housing



1417288

<https://www.phoenixcontact.com/us/products/1417288>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The product photo shows a housing with one outlet

Sleeve housing B6, for single locking latch, material: Die-cast aluminum, cable outlets: 1, lateral, 1x M20, height: 56 mm, cable gland: none

## Commercial data

Item number	1417288
Packing unit	10 pc
Minimum order quantity	50 pc
Product key	AF7AAC
GTIN	4055626083247
Weight per piece (including packing)	151.24 g
Weight per piece (excluding packing)	151 g
Country of origin	DE

# HC-B06-TFL-H-O2STM20S - Housing



1417288

<https://www.phoenixcontact.com/us/products/1417288>

## Technical data


### Notes

General	For contact inserts HC-B6, BB10, DD24, M
---------	--

### Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Type	B6
No. of cable outlets	1
Type of the screw connection	1x M20
Cable outlet	lateral
Pg screw connection	none

### Dimensions

Dimensional drawing	
Width	43 mm
Height	56 mm
Length	60 mm

### Material specifications

Housing material	Die-cast aluminum
Housing surface material	Powder-coated, gray

### Mechanical properties

#### Mechanical data

Type of the screw connection	1x M20
------------------------------	--------

### Mounting

Assembly note	For full screw connections
---------------	----------------------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

# HC-B06-TFL-H-O2STM20S - Housing




1417288

<https://www.phoenixcontact.com/us/products/1417288>

## Drawings

Dimensional drawing



Dimensional drawing

# HC-B06-TFL-H-O2STM20S - Housing



1417288

<https://www.phoenixcontact.com/us/products/1417288>

## Classifications

### ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

# HC-B06-TFL-H-O2STM20S - Housing



1417288

<https://www.phoenixcontact.com/us/products/1417288>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)