

# SAC-5P-M12MS/ 2,0-115 VA - Sensor/actuator cable



1417563

<https://www.phoenixcontact.com/us/products/1417563>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-pos., PUR, RAL 7021 (black gray), straight M12 connector to free cable end, cable length: 2 m, stainless steel knurl

## Commercial data

Item number	1417563
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	AF1CDA
GTIN	4055626115597
Weight per piece (including packing)	80.1 g
Weight per piece (excluding packing)	80.1 g
Country of origin	PL

# SAC-5P-M12MS/ 2,0-115 VA - Sensor/actuator cable



1417563

<https://www.phoenixcontact.com/us/products/1417563>

## Technical data

### Product properties

Product type	Sensor/actuator cable
--------------	-----------------------

### Electrical properties

Nominal voltage $U_N$	48 V AC
	60 V DC

# SAC-5P-M12MS/ 2,0-115 VA - Sensor/actuator cable





1417563

<https://www.phoenixcontact.com/us/products/1417563>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1417563>

 <b>UL Listed</b> Approval ID: FILE E 221474				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	125 V	4 A	-	-

 <b>cUL Listed</b> Approval ID: FILE E 221474				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	125 V	4 A	-	-

# SAC-5P-M12MS/ 2,0-115 VA - Sensor/actuator cable



1417563

<https://www.phoenixcontact.com/us/products/1417563>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

### ETIM

ETIM 10.0	EC001855
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SAC-5P-M12MS/ 2,0-115 VA - Sensor/actuator cable



1417563

<https://www.phoenixcontact.com/us/products/1417563>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)