

# SAC-12P-MS/ 7,5-35T/FS SH SCO - Sensor/actuator cable



1417635

<https://www.phoenixcontact.com/us/products/1417635>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 12-pos., PUR/PVC, RAL 9005 (black), shielded, straight M12 SPEEDCON connector (A-coded) to straight M12 SPEEDCON socket (A-coded), cable length: 7.5 m

## Commercial data

Item number	1417635
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	BF03
Product key	AF1CNA
GTIN	4055626119014
Weight per piece (including packing)	705.9 g
Weight per piece (excluding packing)	730 g
Customs tariff number	85444290
Country of origin	DE

# SAC-12P-MS/ 7,5-35T/FS SH SCO - Sensor/actuator cable



1417635

<https://www.phoenixcontact.com/us/products/1417635>

## Technical data

### Product properties

Product type	Sensor/actuator cable
Shielded	yes

### Electrical properties

Nominal voltage $U_N$	30 V AC
	30 V DC

### Connector

#### Connection 1

Type	Plug straight
------	---------------

#### Connection 2

Type	Socket straight
------	-----------------

# SAC-12P-MS/ 7,5-35T/FS SH SCO - Sensor/actuator cable



1417635

<https://www.phoenixcontact.com/us/products/1417635>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1417635>

 <b>UL Listed</b> Approval ID: E221474				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	30 V	1 A	-	-

# SAC-12P-MS/ 7,5-35T/FS SH SCO - Sensor/actuator cable



1417635

<https://www.phoenixcontact.com/us/products/1417635>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

### ETIM

ETIM 10.0	EC001855
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SAC-12P-MS/ 7,5-35T/FS SH SCO - Sensor/actuator cable



1417635

<https://www.phoenixcontact.com/us/products/1417635>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)