

SAC-12P-MS/ 7,5-35T/FS SH SCO - Sensor/actuator cable



1417635

<https://www.phoenixcontact.com/us/products/1417635>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 12-pos., PUR/PVC, RAL 9005 (black), shielded, straight M12 SPEEDCON connector (A-coded) to straight M12 SPEEDCON socket (A-coded), cable length: 7.5 m

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1417635 |
| Packing unit | 1 pc |
| Minimum order quantity | 50 pc |
| Note | Made to order (non-returnable) |
| Sales key | BF03 |
| Product key | AF1CNA |
| GTIN | 4055626119014 |
| Weight per piece (including packing) | 705.9 g |
| Weight per piece (excluding packing) | 730 g |
| Customs tariff number | 85444290 |
| Country of origin | DE |

SAC-12P-MS/ 7,5-35T/FS SH SCO - Sensor/actuator cable



1417635

<https://www.phoenixcontact.com/us/products/1417635>

Technical data

Product properties

| | |
|--------------|-----------------------|
| Product type | Sensor/actuator cable |
| Shielded | yes |

Electrical properties

| | |
|-----------------------|---------|
| Nominal voltage U_N | 30 V AC |
| | 30 V DC |

Connector

Connection 1

| | |
|------|---------------|
| Type | Plug straight |
|------|---------------|

Connection 2

| | |
|------|-----------------|
| Type | Socket straight |
|------|-----------------|

SAC-12P-MS/ 7,5-35T/FS SH SCO - Sensor/actuator cable



1417635

<https://www.phoenixcontact.com/us/products/1417635>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1417635>

|  UL Listed Approval ID: E221474 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 30 V | 1 A | - | - |

SAC-12P-MS/ 7,5-35T/FS SH SCO - Sensor/actuator cable



1417635

<https://www.phoenixcontact.com/us/products/1417635>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

SAC-12P-MS/ 7,5-35T/FS SH SCO - Sensor/actuator cable



1417635

<https://www.phoenixcontact.com/us/products/1417635>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com