

# CUC-DST-ABK-CP7,5 - Bend protection sleeve



1419794

<https://www.phoenixcontact.com/us/products/1419794>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Bend protection sleeve, degree of protection: IP20, color: black



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1419794       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | AB19          |
| Product key                          | ABNCBZ        |
| GTIN                                 | 4055626188232 |
| Weight per piece (including packing) | 2.14 g        |
| Weight per piece (excluding packing) | 2.04 g        |
| Customs tariff number                | 39269097      |
| Country of origin                    | DE            |

# CUC-DST-ABK-CP7,5 - Bend protection sleeve



1419794

<https://www.phoenixcontact.com/us/products/1419794>

## Technical data

### Product properties

|              |                 |
|--------------|-----------------|
| Product type | Sleeve housings |
|--------------|-----------------|

### Dimensions

|        |         |
|--------|---------|
| Width  | 12.4 mm |
| Height | 14.9 mm |
| Depth  | 17.2 mm |
| Length | 28 mm   |

### Material specifications

|               |                          |
|---------------|--------------------------|
| Color         | black                    |
| Seal material | Thermoplastic elastomers |

### Cable/line

|                         |                   |
|-------------------------|-------------------|
| External cable diameter | 6.2 mm ... 7.6 mm |
|-------------------------|-------------------|

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Degree of protection            | IP20              |
| Ambient temperature (operation) | -35 °C ... 100 °C |

# CUC-DST-ABK-CP7,5 - Bend protection sleeve



1419794

<https://www.phoenixcontact.com/us/products/1419794>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440392 |
| ECLASS-15.0 | 27440392 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002943 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# CUC-DST-ABK-CP7,5 - Bend protection sleeve



1419794

<https://www.phoenixcontact.com/us/products/1419794>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)