

FOC-MODUL:3U-COVER - Central plate



1419977

<https://www.phoenixcontact.com/us/products/1419977>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

3U cover, for 3U fiber optic distribution box



Your advantages

- Modular enclosure design, up to 12 insert modules can be placed into 3U enclosure as required, in order to achieve high packing density FO connection
- The number of insert modules can be freely configured, for module vacancies, there are optional covers to be used with
- Can be flexibly installed in module carrier
- Can be easily extended, thanks to the modular design

Commercial data

Item number	1419977
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB15
Product key	ABNHBZ
GTIN	4055626198293
Weight per piece (including packing)	42 g
Weight per piece (excluding packing)	40 g
Customs tariff number	76169990
Country of origin	CN

1419977

<https://www.phoenixcontact.com/us/products/1419977>

Technical data

Product properties

Product type	Network distributor box
Housing type	Component housing

Dimensions

Width	35.2 mm
Height	128.5 mm
Depth	200 mm

Material specifications

Flammability rating according to UL 94	V0
Ferrule material	PPS
Housing material	Aluminum alloy
Housing surface material	Powder-coated, gray

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-20 °C ... 70 °C

1419977

<https://www.phoenixcontact.com/us/products/1419977>

Classifications

ECLASS

ECLASS-13.0	19170192
ECLASS-15.0	19170192

ETIM

ETIM 10.0	EC003626
-----------	----------

UNSPSC

UNSPSC 21.0	43223300
-------------	----------

FOC-MODUL:3U-COVER - Central plate



1419977

<https://www.phoenixcontact.com/us/products/1419977>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com