

SAC-8P-M12MS/2,0-PUR/M12MR BK - Sensor/actuator cable



1424650

<https://www.phoenixcontact.com/us/products/1424650>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, Plug straight M12, on Plug angled M12

Commercial data

Item number	1424650
Packing unit	1 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	AF1CFA
GTIN	4055626376639
Weight per piece (including packing)	108.9 g
Weight per piece (excluding packing)	105 g
Country of origin	PL

SAC-8P-M12MS/2,0-PUR/M12MR BK - Sensor/actuator cable



1424650

<https://www.phoenixcontact.com/us/products/1424650>

Technical data

Product properties

Product type	Sensor/actuator cable
--------------	-----------------------

Electrical properties

Nominal voltage U_N	30 V AC
	30 V DC

Connector

Connection 1

Type	Plug straight M12
------	-------------------

Connection 2

Type	Plug angled M12
------	-----------------

SAC-8P-M12MS/2,0-PUR/M12MR BK - Sensor/actuator cable





1424650

<https://www.phoenixcontact.com/us/products/1424650>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424650>

 UL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	2 A	-	-

 cUL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	2 A	-	-

SAC-8P-M12MS/2,0-PUR/M12MR BK - Sensor/actuator cable



1424650

<https://www.phoenixcontact.com/us/products/1424650>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-8P-M12MS/2,0-PUR/M12MR BK - Sensor/actuator cable



1424650

<https://www.phoenixcontact.com/us/products/1424650>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com