

# PROT-M12 MS-PA-CHAIN - Screw plug



1430899

<https://www.phoenixcontact.com/us/products/1430899>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

M12 sealing cap with fixing band, for sensor cables, for free M12 sockets



## Commercial data

Item number	1430899
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	BF46
Product key	AF1ZAX
GTIN	4046356332835
Weight per piece (including packing)	4.1 g
Weight per piece (excluding packing)	3.82 g
Customs tariff number	39269097
Country of origin	DE

# PROT-M12 MS-PA-CHAIN - Screw plug



1430899


<https://www.phoenixcontact.com/us/products/1430899>

## Technical data

### Product properties

Product type	Protective cap
Thread type	M12

### Dimensions

Dimensional drawing	
Diameter	20 mm

### Material specifications

Material	PUR (Holding band)
Flammability rating according to UL 94	V0
Seal material	NBR
Material for screw connection	PA 6.6

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C

# PROT-M12 MS-PA-CHAIN - Screw plug




1430899

<https://www.phoenixcontact.com/us/products/1430899>

## Drawings

Dimensional drawing



Dimensional drawing

# PROT-M12 MS-PA-CHAIN - Screw plug



1430899

<https://www.phoenixcontact.com/us/products/1430899>

## Classifications

### ECLASS

ECLASS-13.0	23111190
ECLASS-15.0	27440208

### ETIM

ETIM 10.0	EC002943
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# PROT-M12 MS-PA-CHAIN - Screw plug



1430899

<https://www.phoenixcontact.com/us/products/1430899>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.209 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)