

SAC-4P-M12MSD/10-93P/M12MSDVA - Sensor/actuator cable



1433728

<https://www.phoenixcontact.com/us/products/1433728>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, Plug straight M12, coding: D, on Plug straight M12, coding: D, cable length: 10 m

Commercial data

Item number	1433728
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	AF1CJI
GTIN	4046356448659
Weight per piece (including packing)	491.6 g
Weight per piece (excluding packing)	491.6 g
Country of origin	PL

SAC-4P-M12MSD/10-93P/M12MSDVA - Sensor/actuator cable



1433728

<https://www.phoenixcontact.com/us/products/1433728>

Technical data

Product properties

Product type	Data cable preassembled
--------------	-------------------------

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Connector

Connection 1

Type	Plug straight M12
Number of positions	4
Coding type	D (Data)

Connection 2

Type	Plug straight M12
Number of positions	4
Coding type	D (Data)

Cable/line

Cable length	10 m
--------------	------

SAC-4P-M12MSD/10-93P/M12MSDVA - Sensor/actuator cable



1433728

<https://www.phoenixcontact.com/us/products/1433728>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-4P-M12MSD/10-93P/M12MSDVA - Sensor/actuator cable



1433728

<https://www.phoenixcontact.com/us/products/1433728>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	02dfb3ff-d922-45ae-b959-8273c9cf0440

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com