

# VS-ASI-FC-EPDM-YE 1000M - Flat cable



1434646

<https://www.phoenixcontact.com/us/products/1434646>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



AS-Interface EPDM flat conductor in yellow, 2 x 1.5 mm<sup>2</sup>, 1000 m on a disposable drum

## Commercial data

Item number	1434646
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF11
Product key	AF1LFA
GTIN	4046356349277
Weight per piece (including packing)	60,000 g
Weight per piece (excluding packing)	60,000 g
Customs tariff number	85444995
Country of origin	DE

# VS-ASI-FC-EPDM-YE 1000M - Flat cable



1434646

<https://www.phoenixcontact.com/us/products/1434646>

## Technical data

### Product properties

Product type	Data cable by the meter
Number of positions	2
Shielded	no

### Interfaces

Signal type/category	AS-Interface
----------------------	--------------

### Dimensions

Width	10 mm
Height	4 mm

### Cable/line

Cable length	1000 m
Cable type	Flat cable
Signal type/category	AS-Interface

### FO cable

Transmission medium	Copper
---------------------	--------

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C (Flexibly installed)
	-40 °C ... 85 °C (fixed routing)
Ambient temperature (storage/transport)	-40 °C ... 85 °C

# VS-ASI-FC-EPDM-YE 1000M - Flat cable



1434646

<https://www.phoenixcontact.com/us/products/1434646>

## Classifications

### UNSPSC

UNSPSC 21.0	26121707
-------------	----------

# VS-ASI-FC-EPDM-YE 1000M - Flat cable



1434646

<https://www.phoenixcontact.com/us/products/1434646>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)