

# SAC-3P-12,0-PVC/A-1L-Z - Cable



1438781

<https://www.phoenixcontact.com/us/products/1438781>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable, free cable end, on Valve connector A, with 1 LED, Wiring: Z diode

## Commercial data

Item number	1438781
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	AF1DAA
GTIN	4046356488822
Weight per piece (including packing)	456.7 g
Weight per piece (excluding packing)	452.7 g
Country of origin	PL

# SAC-3P-12,0-PVC/A-1L-Z - Cable



1438781

<https://www.phoenixcontact.com/us/products/1438781>

## Technical data

### Product properties

Product type	Sensor/actuator cable with valve connector
--------------	--

### Electrical properties

Nominal voltage $U_N$	24 V AC
	24 V DC

### Connector

#### Connection 1

Type	free cable end
------	----------------

#### Connection 2

Type	Valve connector A
Protective circuit	Z diode

# SAC-3P-12,0-PVC/A-1L-Z - Cable





1438781

<https://www.phoenixcontact.com/us/products/1438781>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1438781>

 <b>CSA</b> Approval ID: 13631				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	24 V	4 A	-	-

 <b>CSAus</b> Approval ID: 13631				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	24 V	4 A	-	-

# SAC-3P-12,0-PVC/A-1L-Z - Cable



1438781

<https://www.phoenixcontact.com/us/products/1438781>

## Classifications

### ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

### ETIM

ETIM 10.0	EC001855
-----------	----------

### UNSPSC

UNSPSC 21.0	31251500
-------------	----------

# SAC-3P-12,0-PVC/A-1L-Z - Cable



1438781

<https://www.phoenixcontact.com/us/products/1438781>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Diboron trioxide(CAS: 1303-86-2)
	Lead monoxide (lead oxide)(CAS: 1317-36-8)

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)