

# SAC-3P-M12MR/0,6-PUR/C-1L-Z - Cable



1439463

<https://www.phoenixcontact.com/us/products/1439463>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable, Plug angled M12, coding: A, on Valve connector C (8 mm), with 1 LED, Wiring: Z diode

## Commercial data

Item number	1439463
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF07
Product key	AF1DNA
GTIN	4046356511643
Weight per piece (including packing)	42 g
Weight per piece (excluding packing)	40.7 g
Customs tariff number	85444290
Country of origin	PL

# SAC-3P-M12MR/0,6-PUR/C-1L-Z - Cable



1439463

<https://www.phoenixcontact.com/us/products/1439463>

## Technical data

### Product properties

Product type	Sensor/actuator cable with valve connector
--------------	--

### Electrical properties

Nominal voltage $U_N$	24 V AC
	24 V DC

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	$\geq 100$
-----------------------------	------------

### Connector

#### Connection 1

Type	Plug angled M12
Coding type	A

#### Connection 2

Type	Valve connector C (8 mm)
Protective circuit	Z diode

# SAC-3P-M12MR/0,6-PUR/C-1L-Z - Cable



1439463

<https://www.phoenixcontact.com/us/products/1439463>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1439463>



**EAC-RoHS**

Approval ID: RU D-DE.HB35.B.00387



**CSAus**

Approval ID: 13631

	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	24 V	4 A	-	-

# SAC-3P-M12MR/0,6-PUR/C-1L-Z - Cable



1439463

<https://www.phoenixcontact.com/us/products/1439463>

## Classifications

### ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

### ETIM

ETIM 10.0	EC001855
-----------	----------

### UNSPSC

UNSPSC 21.0	31251500
-------------	----------

1439463

<https://www.phoenixcontact.com/us/products/1439463>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Diboron trioxide(CAS: 1303-86-2)
	Lead monoxide (lead oxide)(CAS: 1317-36-8)

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)