

# SAC-4P- 4,0-PVC/M12FR - Sensor/actuator cable



1447112

<https://www.phoenixcontact.com/us/products/1447112>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-pos., PVC, RAL 7021 (black-gray), free cable end, to angled M12 socket, A-coded, cable length: 4.0 m

## Commercial data

Item number	1447112
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CCA
GTIN	4046356661393
Weight per piece (including packing)	148.178 g
Weight per piece (excluding packing)	148.178 g
Country of origin	DE

# SAC-4P- 4,0-PVC/M12FR - Sensor/actuator cable



1447112

<https://www.phoenixcontact.com/us/products/1447112>

## Technical data

### Product properties

Product type	Sensor/actuator cable
--------------	-----------------------

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Electrical properties

Nominal voltage $U_N$	250 V AC
	250 V DC
Nominal current $I_N$	4 A

### Connection data

#### Conductor connection

Tightening torque	0.4 Nm
-------------------	--------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
	IP67

# SAC-4P- 4,0-PVC/M12FR - Sensor/actuator cable



1447112

<https://www.phoenixcontact.com/us/products/1447112>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

# SAC-4P- 4,0-PVC/M12FR - Sensor/actuator cable



1447112

<https://www.phoenixcontact.com/us/products/1447112>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)