

SAC-2P-M 8MS/ 0,6-PUR/ZC-1L-S - Sensor/actuator cable



1453326

<https://www.phoenixcontact.com/us/products/1453326>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 2-position, PUR, gray RAL 7001, Plug straight M8, on Valve connector Festo ZC, with 1 LED, Wiring: Protective circuit and holding current reduction, cable length: 0.6 m

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Connecting cable specially for Festo KMYZ9 type valves

Commercial data

Item number	1453326
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF08
Product key	AF1DWA
GTIN	4046356551038
Weight per piece (including packing)	15.3 g
Weight per piece (excluding packing)	14.55 g
Customs tariff number	85444290
Country of origin	PL

SAC-2P-M 8MS/ 0,6-PUR/ZC-1L-S - Sensor/actuator cable



1453326

<https://www.phoenixcontact.com/us/products/1453326>

Technical data

Product properties

Product type	Sensor/actuator cable with valve connector
Application	Standard
Number of positions	2
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Connection data

Conductor connection

Tightening torque	0.2 Nm (M8 connectors)
-------------------	------------------------

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material housing valve plug	PA
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Contact material	CuSn
Contact surface material	Sn
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	24 V DC
Nominal current I_N	4 A

Valve connector characteristics

Fixing screws	M2
---------------	----

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	1 LED
Status display present	yes

SAC-2P-M 8MS/ 0,6-PUR/ZC-1L-S - Sensor/actuator cable



1453326

<https://www.phoenixcontact.com/us/products/1453326>

Connector

Connection 1

Type	Plug straight M8
Material	CuSn (Contact)
	Ni/Au (Contact surface)
	TPU GF (Contact carrier)
	TPU, hardly inflammable, self-extinguishing (Grip body)


Connection 2

Type	Valve connector Festo ZC
Material	CuSn (Contact)
	Sn (Contact surface)
	PA (Housing)
Protective circuit	Protective circuit and holding current reduction

Cable/line

Cable length	0.6 m
--------------	-------

PUR gray [PUR]

Dimensional drawing	
Number of positions	2
Shielded	no
Cable type	PUR gray [PUR]
AWG signal line	24
Conductor cross-section	2x 0.25 mm ² (Signal line)
External cable diameter	3.40 mm
Outer sheath, material	PUR
External sheath, color	gray RAL 7001
Conductor material	Bare Cu litz wires
Single wire, color	black, black
Ambient temperature (operation)	-10 °C ... 50 °C (cable, fixed installation)
	-10 °C ... 50 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

IP65

SAC-2P-M 8MS/ 0,6-PUR/ZC-1L-S - Sensor/actuator cable



1453326

<https://www.phoenixcontact.com/us/products/1453326>

Degree of protection	IP67
	IP68
Ambient temperature (operation) (Valve connector)	-10 °C ... 50 °C (Valve connector)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)

SAC-2P-M 8MS/ 0,6-PUR/ZC-1L-S - Sensor/actuator cable




1453326


<https://www.phoenixcontact.com/us/products/1453326>

Drawings

Dimensional drawing



Dimensional drawing




SAC-2P-M 8MS/ 0,6-PUR/ZC-1L-S - Sensor/actuator cable


1453326

<https://www.phoenixcontact.com/us/products/1453326>

Dimensional drawing



Schematic diagram



SAC-2P-M 8MS/ 0,6-PUR/ZC-1L-S - Sensor/actuator cable



1453326

<https://www.phoenixcontact.com/us/products/1453326>

Schematic diagram



SAC-2P-M 8MS/ 0,6-PUR/ZC-1L-S - Sensor/actuator cable



1453326

<https://www.phoenixcontact.com/us/products/1453326>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1453326>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

SAC-2P-M 8MS/ 0,6-PUR/ZC-1L-S - Sensor/actuator cable



1453326

<https://www.phoenixcontact.com/us/products/1453326>

Classifications

ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

SAC-2P-M 8MS/ 0,6-PUR/ZC-1L-S - Sensor/actuator cable



1453326

<https://www.phoenixcontact.com/us/products/1453326>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	2.583 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com