

# PROT-M12 FS-PA-CHAIN-EYE-DM14 - Sealing cap



1456190

<https://www.phoenixcontact.com/us/products/1456190>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M12 sealing cap made of plastic with fixing band, for free M12 plugs with 14.5 mm fastening eye

## Commercial data

Item number	1456190
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	AB28
Product key	ABQZAA
GTIN	4046356605717
Weight per piece (including packing)	4.68 g
Weight per piece (excluding packing)	4.05 g
Customs tariff number	39269097
Country of origin	DE

# PROT-M12 FS-PA-CHAIN-EYE-DM14 - Sealing cap



1456190

<https://www.phoenixcontact.com/us/products/1456190>

## Technical data

### Product properties

Product type	Protective cap
Thread type	M12

### Material specifications

Material	PA / TPU
	PUR (Holding band)
Flammability rating according to UL 94	V0 / HB
Seal material	NBR

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C

# PROT-M12 FS-PA-CHAIN-EYE-DM14 - Sealing cap



1456190

<https://www.phoenixcontact.com/us/products/1456190>

## Classifications

### ECLASS

ECLASS-13.0	27440208
ECLASS-15.0	27440208

### ETIM

ETIM 10.0	EC002314
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# PROT-M12 FS-PA-CHAIN-EYE-DM14 - Sealing cap



1456190

<https://www.phoenixcontact.com/us/products/1456190>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.222 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)