

HC-B 06-SMLD-74/O1M25 - Housing



1460032

<https://www.phoenixcontact.com/us/products/1460032>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Box mounting base, with single locking latch, height: 74 mm, with 1 x M25 gland, with protective cover

Commercial data

Item number	1460032
Packing unit	10 pc
Minimum order quantity	1 pc
Product key	AF7AAC
GTIN	4046356696609
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	DE

HC-B 06-SMLD-74/O1M25 - Housing

1460032

<https://www.phoenixcontact.com/us/products/1460032>

Technical data


Notes

General	For contact inserts HC-B16, BB32, D40, DD72, HS6, M, K
---------	--

Product properties

Housing type	Surface mounting housing
Type	B6
No. of cable outlets	1
Type of the screw connection	1x M25
Protective cover	yes
Cable outlet	left (view of the opened single locking latch)
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	57 mm
Height	67 mm
Length	117 mm

Material specifications

Seal material	NBR
Housing material	Die-cast aluminum
Housing surface material	Powder-coated, gray
Material, protective cover	PA
Locking latch material	Stainless steel, handle: PA

Mechanical properties

Mechanical data

Type of the screw connection	1x M25
------------------------------	--------

Mounting

Assembly note	For half and full screw connections
---------------	-------------------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (When plugged in)
	IP54 (with closed protective cover)

HC-B 06-SMLD-74/O1M25 - Housing



1460032

<https://www.phoenixcontact.com/us/products/1460032>

Ambient temperature (operation)

-40 °C ... 125 °C

HC-B 06-SMLD-74/O1M25 - Housing




1460032

<https://www.phoenixcontact.com/us/products/1460032>

Drawings

Dimensional drawing



Dimensional drawing

HC-B 06-SMLD-74/O1M25 - Housing



1460032

<https://www.phoenixcontact.com/us/products/1460032>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1460032>



EAC

Approval ID: RU C-DE.AI30.B.01102

HC-B 06-SMLD-74/O1M25 - Housing



1460032

<https://www.phoenixcontact.com/us/products/1460032>

Classifications

ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

HC-B 06-SMLD-74/O1M25 - Housing



1460032

<https://www.phoenixcontact.com/us/products/1460032>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com