

# HC-B 24-TFL-H-M1M32G - Housing

1460099

<https://www.phoenixcontact.com/us/products/1460099>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON B24 sleeve housing, for single locking latch, height: 76 mm, with 1 x M32 screw connection, straight cable outlet

## Commercial data

Item number	1460099
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF55
Product key	AF7AAC
GTIN	4046356793476
Weight per piece (including packing)	314 g
Weight per piece (excluding packing)	314 g
Customs tariff number	85389099
Country of origin	DE

# HC-B 24-TFL-H-M1M32G - Housing

1460099


<https://www.phoenixcontact.com/us/products/1460099>

## Technical data

### Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Type	B24
No. of cable outlets	1
Type of the screw connection	1x M32
Cable outlet	straight
Pg screw connection	with

### Dimensions

Dimensional drawing	
Width	43 mm
Height	76 mm
Length	120 mm
Wrench size, union nut	32 mm

### Material specifications

Seal material Cable seal	NBR
Housing material	Die-cast aluminum
Housing surface material	Powder-coated, gray
Material for screw connection	Brass

### Mechanical properties

#### Mechanical data

Type of the screw connection	1x M32
------------------------------	--------

### Cable/line

External cable diameter	16 mm ... 21 mm
-------------------------	-----------------

### Connection data

External cable diameter	16 mm ... 21 mm
-------------------------	-----------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

# HC-B 24-TFL-H-M1M32G - Housing


1460099

<https://www.phoenixcontact.com/us/products/1460099>



## Drawings

Dimensional drawing



Dimensional drawing

# HC-B 24-TFL-H-M1M32G - Housing



1460099

<https://www.phoenixcontact.com/us/products/1460099>

## Classifications

### ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

# HC-B 24-TFL-H-M1M32G - Housing



1460099

<https://www.phoenixcontact.com/us/products/1460099>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)