

HC-B 16-SMQ-84/O2M40 - Housing

1460169

<https://www.phoenixcontact.com/us/products/1460169>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON B16 box mounting base, with double locking latch, height: 84 mm, with 2 x M40 glands

Commercial data

Item number	1460169
Packing unit	10 pc
Minimum order quantity	1 pc
Product key	AF7AAC
GTIN	4046356696661
Weight per piece (including packing)	383.2 g
Weight per piece (excluding packing)	350 g
Country of origin	DE

HC-B 16-SMQ-84/O2M40 - Housing

1460169


<https://www.phoenixcontact.com/us/products/1460169>

Technical data

Product properties

Product type	Housing with locking latch
Housing type	Surface mounting housing
Application	Standard
Type	B16
No. of cable outlets	2
Type of the screw connection	2x M40
Shielded	no
Cable outlet	lateral
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	57 mm
Height	84 mm
Length	117 mm

Material specifications

Seal material	NBR
Housing material	Die-cast aluminum
Housing surface material	Powder-coated, gray
Locking latch material	Stainless steel, handle: PA

Mechanical properties

Mechanical data

Type of the screw connection	2x M40
Locking type	Latch

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

HC-B 16-SMQ-84/O2M40 - Housing




1460169

<https://www.phoenixcontact.com/us/products/1460169>

Drawings

Dimensional drawing



Dimensional drawing

HC-B 16-SMQ-84/O2M40 - Housing



1460169

<https://www.phoenixcontact.com/us/products/1460169>

Classifications

ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

UNSPSC

UNSPSC 21.0	31261501
-------------	----------

HC-B 16-SMQ-84/O2M40 - Housing



1460169

<https://www.phoenixcontact.com/us/products/1460169>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com