

# HC-B 10-TMB-100/O1STM25S-EEE - Housing



1460366

<https://www.phoenixcontact.com/us/products/1460366>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON ADVANCE B10 sleeve housing, with bayonet locking (Allen screw), salt water resistant aluminum, height: 100 mm, with 1 x M25 thread, lateral cable outlet, without surface; conductive seal (EMC properties)

## Commercial data

Item number	1460366
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF58
Product key	AF7AAA
GTIN	4046356592659
Weight per piece (including packing)	500 g
Weight per piece (excluding packing)	500 g
Customs tariff number	85389099
Country of origin	DE

1460366

<https://www.phoenixcontact.com/us/products/1460366>

## Technical data


### Notes

General	For contact inserts HC-B10, BB18, DD42, M, K8/24
---------	--------------------------------------------------

### Product properties

Product type	Housing with bayonet locking
Housing type	Sleeve housing
Application	Offshore/EMC
Type	B10
No. of cable outlets	1
Type of the screw connection	1x M25
Fixing screws	M6
Shielded	yes
Cable outlet	lateral
Pg screw connection	none

### Dimensions

Dimensional drawing	
Width	57 mm
Height	100 mm
Length	105 mm

### Material specifications

Seal material	NBR, conductive
Housing material	Die-cast aluminum, corrosion resistant
Housing surface material	uncoated
Locking latch material	Stainless steel

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP66
	IP67
Ambient temperature (operation)	-40 °C ... 125 °C

### Mechanical properties

#### Mechanical data

Type of the screw connection	1x M25
Locking type	Screw

# HC-B 10-TMB-100/O1STM25S-EEE - Housing



1460366

<https://www.phoenixcontact.com/us/products/1460366>

## Mounting

Assembly note	If insulating powder coating is present on the control cabinet panel, it should be removed from the profile gasket area in order to ensure optimum shielding.
Fixing screws	M6


# HC-B 10-TMB-100/O1STM25S-EEE - Housing

1460366

<https://www.phoenixcontact.com/us/products/1460366>

## Drawings

Dimensional drawing



Dimensional drawing

Dimensional drawing



Panel cutout

<sup>2)</sup> when self-tapping screws are used (Torx® 20, M4)

# HC-B 10-TMB-100/O1STM25S-EEE - Housing



1460366

<https://www.phoenixcontact.com/us/products/1460366>

## Classifications

### ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

# HC-B 10-TMB-100/O1STM25S-EEE - Housing



1460366

<https://www.phoenixcontact.com/us/products/1460366>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)