

OCS MOUNT 1210 SET - Wall bracket



1471782

<https://www.phoenixcontact.com/us/products/1471782>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting plate, set of 2 pieces incl. screws for housing size of 12" x 10", material: polycarbonate, color: light gray



Your advantages

- Internationally certified housing system
- Special plastic enables safe continuous operation
- Provides protection against the ingress of jet water
- Withstands even heavy mechanical strain

Commercial data

Item number	1471782
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC04
Product key	ACFDBZ
GTIN	4063151881320
Weight per piece (including packing)	164.266 g
Weight per piece (excluding packing)	159 g
Customs tariff number	39269097
Country of origin	EE

OCS MOUNT 1210 SET - Wall bracket



1471782

<https://www.phoenixcontact.com/us/products/1471782>

Technical data

Notes

Assembly note	Only use the screws supplied for mounting.
Assembly note	Secure the mounting feet or flanges using the screws provided. If mounting the housing on a wall, select the appropriate screw type for the wall construction.

Product properties

Product type	Mounting material
Housing type	Outdoor housing
Housing type	Outdoor housings
Housing series	OCS
Product family	OCS..1210..

Dimensions

Width	65 mm
Height	255 mm
Depth	8 mm

Material specifications

Color	light gray (RAL 7035)
Material	PC
Flammability rating according to UL 94	V2
Insulating material	PC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

Mounting

Mounting type	Screw mounting
---------------	----------------

Packaging specifications

Type of packaging	PE bag
-------------------	--------

OCS MOUNT 1210 SET - Wall bracket



1471782

<https://www.phoenixcontact.com/us/products/1471782>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1471782>

FI Cert

Approval ID: FI/42054

OCS MOUNT 1210 SET - Wall bracket



1471782

<https://www.phoenixcontact.com/us/products/1471782>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

OCS MOUNT 1210 SET - Wall bracket



1471782

<https://www.phoenixcontact.com/us/products/1471782>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com