

OCS POLEFIX 1008 - Mounting material



1476924

<https://www.phoenixcontact.com/us/products/1476924>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mount for mast Ø of 60 mm ... 140 mm, complete set for a housing of 10" x 8", material: steel



Your advantages

- Internationally certified housing system
- Special plastic enables safe continuous operation
- Provides protection against the ingress of jet water
- Withstands even heavy mechanical strain

Commercial data

Item number	1476924
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC04
Product key	ACFDBZ
GTIN	4063151897208
Weight per piece (including packing)	0.746 kg
Weight per piece (excluding packing)	0.664 kg
Customs tariff number	73269098
Country of origin	EE

OCS POLEFIX 1008 - Mounting material



1476924

<https://www.phoenixcontact.com/us/products/1476924>

Technical data

Product properties

Product type	Mounting material
Housing type	Outdoor housing
Housing type	Outdoor housings
Housing series	OCS
Product family	OCS..1008..

Dimensions

Width	197 mm
Height	326 mm

Material specifications

Color	silver-colored
Material	Steel
Surface characteristics	galvanized

Mounting

Mounting type	Mast mounting or panel mounting
---------------	---------------------------------

Packaging specifications

Type of packaging	Box packaging
-------------------	---------------

OCS POLEFIX 1008 - Mounting material



1476924

<https://www.phoenixcontact.com/us/products/1476924>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

OCS POLEFIX 1008 - Mounting material



1476924

<https://www.phoenixcontact.com/us/products/1476924>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com