

PRC 20 SEAL 8-10 SET 25 - Insert seal



1532208

<https://www.phoenixcontact.com/us/products/1532208>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insert seal, Range of articles: PRC 20, color: black, min. cable diameter: 8 mm, max. cable diameter: 10 mm

Your advantages

- Up to 75% smaller in size than industrial connectors with the same rating
- Locking mechanism can be unlocked manually or using a tool
- Suitable for applications in atmospheres containing salt and in direct sunlight
- Ideal for indoor and outdoor use due to weatherproof materials

Commercial data

Item number	1532208
Packing unit	25 pc
Minimum order quantity	100 pc
Product key	ABLHBA
GTIN	4067923001534
Weight per piece (including packing)	1.65 g
Weight per piece (excluding packing)	1.548 g
Country of origin	DE

PRC 20 SEAL 8-10 SET 25 - Insert seal



1532208

<https://www.phoenixcontact.com/us/products/1532208>

Technical data

Product properties

Product type	Seal
Product family	PRC 20

Dimensions

Width	17.5 mm
Height	17.5 mm
Length	9.6 mm

Material specifications

Color	black (RAL 9005)
Material Seal	EPDM (Cable seal)

Cable/line

External cable diameter	8 mm ... 10 mm
Halogen-free	yes (in accordance with IEC 61249-2-21:2003- 11 Cl.3.1)

Environmental and real-life conditions

Ambient conditions

Category of shock impact	IK08 (-25°C)
Ambient temperature (operation)	-40 °C ... 105 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 85 °C

PRC 20 SEAL 8-10 SET 25 - Insert seal



1532208

<https://www.phoenixcontact.com/us/products/1532208>

Classifications

ECLASS

ECLASS-13.0	27440691
ECLASS-15.0	27440691

ETIM

ETIM 10.0	EC002863
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PRC 20 SEAL 8-10 SET 25 - Insert seal



1532208

<https://www.phoenixcontact.com/us/products/1532208>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.039 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com