

SACC-DSIP-M12MS-4CON-L180-SI - Device connector rear mounting



1528235

<https://www.phoenixcontact.com/us/products/1528235>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator flush-type plug, 4-pos., M12, A-coded, front/press-in mounting, with straight solder connection

Commercial data

Item number	1528235
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AB26
Product key	ABQEGI
GTIN	4046356023214
Weight per piece (including packing)	22.28 g
Weight per piece (excluding packing)	22.28 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSIP-M12MS-4CON-L180-SI - Device connector rear mounting



1528235

<https://www.phoenixcontact.com/us/products/1528235>

Technical data

Product properties

Product type	Circular connectors (device side)
Number of positions	4
Shielded	no
Coding	A
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Material Housing	CuZn
Material Housing surface	Ni
Material Insulating body	PBT
Material Contact	CuZn
Material Contact surface	Au
Material Seal	NBR
Flammability rating according to UL 94	V0

Electrical properties

Contact resistance	$\leq 0.003 \Omega$
Insulation resistance	$\geq 1 T\Omega$
Nominal voltage U_N	250 V
Nominal current I_N	4 A

Connection data

Conductor connection

Connection method	Solder pins
-------------------	-------------

Connector

Connection 1

Head design	Plug
Head cable outlet	straight
Head thread type	M12
Coding	A

Cable/line

Signal type/category	Universal
----------------------	-----------

SACC-DSIP-M12MS-4CON-L180-SI - Device connector rear mounting



1528235

<https://www.phoenixcontact.com/us/products/1528235>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)

SACC-DSIP-M12MS-4CON-L180-SI - Device connector rear mounting

1528235

<https://www.phoenixcontact.com/us/products/1528235>

Drawings

Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

SACC-DSIP-M12MS-4CON-L180-SI - Device connector rear mounting



1528235

<https://www.phoenixcontact.com/us/products/1528235>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 9.0	EC003568
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSIP-M12MS-4CON-L180-SI - Device connector rear mounting



1528235

<https://www.phoenixcontact.com/us/products/1528235>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com