

PROT-M5 - Screw plug

1533288

<https://www.phoenixcontact.com/us/products/1533288>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



An M5 screw plug for the unoccupied M5 sockets of the sensor/actuator cable, boxes and flush-type connectors

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1533288 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BF45 |
| Product key | AF3ZAX |
| GTIN | 4017918993528 |
| Weight per piece (including packing) | 0.3 g |
| Weight per piece (excluding packing) | 0.3 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

PROT-M5 - Screw plug

1533288

<https://www.phoenixcontact.com/us/products/1533288>



Technical data

Product properties

| | |
|--------------|----------------------------|
| Product type | Plug for cable screw gland |
| Application | Sensor/actuator box |
| Thread type | M5 |

Material specifications

| | |
|----------|----|
| Material | PA |
|----------|----|

Environmental and real-life conditions

Ambient conditions

| | |
|----------------------|------|
| Degree of protection | IP65 |
| | IP67 |

PROT-M5 - Screw plug


1533288

<https://www.phoenixcontact.com/us/products/1533288>



Drawings

Dimensional drawing



PROT-M5 - Screw plug



1533288

<https://www.phoenixcontact.com/us/products/1533288>

Environmental product compliance

EU RoHS

| | |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

China RoHS

| | |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com