

# SAC-5P-M12MS CAN TR 2X120 OHM - Termination resistor



1543728

<https://www.phoenixcontact.com/us/products/1543728>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Terminating resistor CANopen®/DeviceNet™ M12, 2x 120 Ω

## Commercial data

Item number	1543728
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	BF10
Product key	AF1GVX
GTIN	4046356103770
Weight per piece (including packing)	11.493 g
Weight per piece (excluding packing)	8.12 g
Customs tariff number	85332100
Country of origin	DE

# SAC-5P-M12MS CAN TR 2X120 OHM - Termination resistor



1543728

<https://www.phoenixcontact.com/us/products/1543728>

## Technical data

### Product properties

Product type	Terminal resistor
Number of positions	5
Coding	A

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Electrical properties

Nominal voltage $U_N$	48 V AC
	60 V DC
	5 V <sub>rms</sub>
Nominal current $I_N$	4 A

### Signaling

Status display	no
Status display present	no

### Material specifications

Flammability rating according to UL 94	HB
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

### Connector

#### Connection 1

Type	Plug straight M12
Number of positions	5
Coding type	A

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
	IP67

# SAC-5P-M12MS CAN TR 2X120 OHM - Termination resistor



1543728

<https://www.phoenixcontact.com/us/products/1543728>

Ambient temperature (operation)

-25 °C ... 90 °C (Plug)


# SAC-5P-M12MS CAN TR 2X120 OHM - Termination resistor

1543728

<https://www.phoenixcontact.com/us/products/1543728>

## Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

# SAC-5P-M12MS CAN TR 2X120 OHM - Termination resistor



1543728

<https://www.phoenixcontact.com/us/products/1543728>

## Classifications

### ECLASS

ECLASS-13.0	19070403
ECLASS-15.0	19070403

### ETIM

ETIM 10.0	EC000448
-----------	----------

### UNSPSC

UNSPSC 21.0	32121600
-------------	----------

# SAC-5P-M12MS CAN TR 2X120 OHM - Termination resistor



1543728

<https://www.phoenixcontact.com/us/products/1543728>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.251 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)