

SAC-5P- 0,7-927/FS SCO JLG - Bus system cable



1573662

<https://www.phoenixcontact.com/us/products/1573662>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, free cable end, on Socket straight M12 SPEEDCON, coding: A

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1573662 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BF04 |
| Product key | AF1CDD |
| GTIN | 4046356445269 |
| Weight per piece (including packing) | 85.7 g |
| Weight per piece (excluding packing) | 85.7 g |
| Customs tariff number | 85444290 |
| Country of origin | PL |

SAC-5P- 0,7-927/FS SCO JLG - Bus system cable



1573662

<https://www.phoenixcontact.com/us/products/1573662>

Technical data

Product properties

| | |
|--------------|-------------------------|
| Product type | Data cable preassembled |
|--------------|-------------------------|

Electrical properties

| | |
|-----------------------|---------|
| Nominal voltage U_N | 48 V AC |
| | 60 V DC |

Connector

Connection 1

| | |
|------|----------------|
| Type | free cable end |
|------|----------------|

Connection 2

| | |
|---------------------|------------------------------|
| Type | Socket straight M12 SPEEDCON |
| Number of positions | 5 |
| Locking type | SPEEDCON |
| Coding type | A (Standard) |

SAC-5P- 0,7-927/FS SCO JLG - Bus system cable



1573662

<https://www.phoenixcontact.com/us/products/1573662>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

1573662

<https://www.phoenixcontact.com/us/products/1573662>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com