

SAC-3P-10,0-500/A-1L-Z KA - Sensor/actuator cable



1579527

<https://www.phoenixcontact.com/us/products/1579527>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, free cable end, on Valve connector A, with 1 LED

Commercial data

Item number	1579527
Packing unit	25 pc
Minimum order quantity	25 pc
Product key	AF1DAA
GTIN	4046356513746
Weight per piece (including packing)	450 g
Weight per piece (excluding packing)	450 g
Country of origin	PL

SAC-3P-10,0-500/A-1L-Z KA - Sensor/actuator cable



1579527

<https://www.phoenixcontact.com/us/products/1579527>

Technical data

Product properties

Product type	Sensor/actuator cable with valve connector
--------------	--

Electrical properties

Nominal voltage U_N	24 V AC
	24 V DC

Signaling

Status display	1 LED
----------------	-------

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Valve connector A
------	-------------------

SAC-3P-10,0-500/A-1L-Z KA - Sensor/actuator cable




1579527

<https://www.phoenixcontact.com/us/products/1579527>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1579527>

 CSAus Approval ID: 13631				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	24 V	4 A	-	-

SAC-3P-10,0-500/A-1L-Z KA - Sensor/actuator cable



1579527

<https://www.phoenixcontact.com/us/products/1579527>

Classifications

ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

SAC-3P-10,0-500/A-1L-Z KA - Sensor/actuator cable



1579527

<https://www.phoenixcontact.com/us/products/1579527>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	5.558 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com