

# VC-AL-T3-Z-M32-S - Housing

1583694

<https://www.phoenixcontact.com/us/products/1583694>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Aluminum die-cast sleeve housing, with grommet, locking screws with cylinder head, for a metric M32 cable gland, angled cable outlet, type VC3

The figure shows the product version with knurled screw

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1583694                        |
| Packing unit                         | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AB01                           |
| Product key                          | ABLAAX                         |
| GTIN                                 | 4046356183321                  |
| Weight per piece (including packing) | 271.58 g                       |
| Weight per piece (excluding packing) | 150 g                          |
| Customs tariff number                | 85389099                       |
| Country of origin                    | PL                             |

# VC-AL-T3-Z-M32-S - Housing

1583694

<https://www.phoenixcontact.com/us/products/1583694>

## Technical data


### Notes

|         |   |
|---------|---|
| General | When using fiber optics, the bending radii of the cable manufacturers must be observed. |
|---------|---|

### Product properties

|                              |                 |
|------------------------------|-----------------|
| Product type                 | Sleeve housings |
| Product family               | VARIOCON        |
| Type                         | VC3             |
| No. of cable outlets         | 1               |
| Type of the screw connection | M32 x 1.5       |
| Fixing screws                | M4              |
| Shielded                     | no              |
| Cable outlet                 | slanted         |

### Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Width               | 38 mm  |
| Height              | 85 mm  |
| Length              | 94 mm  |

### Material specifications

|  |                   |
|--|-------------------|
| Color                                  | gray aluminum     |
| Flammability rating according to UL 94 | V0                |
| Seal material                          | NBR, conductive   |
| Housing material                       | Die-cast aluminum |
| O-ring material                        | NBR               |
| Material of locking screw              | V2A               |

### Mechanical properties

#### Mechanical data

|                              |           |
|------------------------------|-----------|
| Type of the screw connection | M32 x 1.5 |
| Locking type                 | Screw     |

### Environmental and real-life conditions

#### Ambient conditions

|                      |      |
|----------------------|------|
| Degree of protection | IP65 |
|----------------------|------|

# VC-AL-T3-Z-M32-S - Housing



1583694

<https://www.phoenixcontact.com/us/products/1583694>

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

## Mounting

|               |    |
|---------------|----|
| Fixing screws | M4 |
|---------------|----|


# VC-AL-T3-Z-M32-S - Housing

1583694


<https://www.phoenixcontact.com/us/products/1583694>

## Drawings

Dimensional drawing



Dimensional drawing




# VC-AL-T3-Z-M32-S - Housing

1583694

<https://www.phoenixcontact.com/us/products/1583694>



Dimensional drawing



# VC-AL-T3-Z-M32-S - Housing



1583694

<https://www.phoenixcontact.com/us/products/1583694>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)