

HC-B 10-SD-MQT/FS-AL - Protective cover



1584541

<https://www.phoenixcontact.com/us/products/1584541>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Protective cover B10, with double locking latch, protective cover material: Al, height: 16.9 mm, seal: yes, with lanyard



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1584541 |
| Packing unit | 1 pc |
| Sales key | BF66 |
| Product key | AF7AZC |
| GTIN | 4046356144131 |
| Weight per piece (including packing) | 107.81 g |
| Weight per piece (excluding packing) | 107.81 g |
| Customs tariff number | 85389099 |
| Country of origin | DE |

HC-B 10-SD-MQT/FS-AL - Protective cover

1584541


<https://www.phoenixcontact.com/us/products/1584541>

Technical data

Product properties

| | |
|------------------------|------------------|
| Product type | Protective cover |
| Housing type | Protective cover |
| Type | B10 |
| Retaining cord present | yes |
| Seal present | yes |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 43 mm |
| Height | 16.9 mm |
| Length | 73 mm |
| Diameter | 30 mm |

Material specifications

| | |
|----------------------------|-----------------------------------|
| Material Protective cover | Die-cast aluminum (powder-coated) |
| Seal material | NBR |
| Housing surface material | Powder-coated, gray |
| Material, protective cover | Al |
| Locking latch material | High-grade steel, handle: PA-GF |

Mechanical properties

Mechanical data

| | |
|--------------|-------|
| Locking type | Latch |
|--------------|-------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Degree of protection | IP66 |
| Ambient temperature (operation) | -40 °C ... 125 °C |

Mounting

| | |
|---------------|---|
| Assembly note | Not for HC-B...EMC housings The guide pins of the protective cover must be removed when using coding sockets, pins, and bolts. |
|---------------|---|

HC-B 10-SD-MQT/FS-AL - Protective cover




1584541

<https://www.phoenixcontact.com/us/products/1584541>

Drawings

Dimensional drawing



Dimensional drawing

HC-B 10-SD-MQT/FS-AL - Protective cover



1584541

<https://www.phoenixcontact.com/us/products/1584541>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440208 |
| ECLASS-15.0 | 27440208 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

HC-B 10-SD-MQT/FS-AL - Protective cover



1584541

<https://www.phoenixcontact.com/us/products/1584541>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com