

# HC-B 16-SD-MQT/FS-AL - Protective cover



1584554

<https://www.phoenixcontact.com/us/products/1584554>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Protective cover B16, with double locking latch, protective cover material: Al, height: 16.9 mm, seal: yes, with lanyard



## Commercial data

Item number	1584554
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BF66
Product key	AF7AZC
GTIN	4046356145060
Weight per piece (including packing)	120 g
Weight per piece (excluding packing)	115.92 g
Customs tariff number	85389099
Country of origin	DE

# HC-B 16-SD-MQT/FS-AL - Protective cover



1584554


<https://www.phoenixcontact.com/us/products/1584554>

## Technical data

### Product properties

Product type	Protective cover
Housing type	Protective cover
Type	B16
Retaining cord present	yes
Seal present	yes

### Dimensions

Dimensional drawing	
Width	43 mm
Height	16.9 mm
Length	93.5 mm
Diameter	30 mm

### Material specifications

Material Protective cover	Die-cast aluminum (powder-coated)
Seal material	NBR
Housing surface material	Powder-coated, gray
Material, protective cover	Al
Locking latch material	High-grade steel, handle: PA-GF

### Mechanical properties

#### Mechanical data

Locking type	Latch
--------------	-------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP66
Ambient temperature (operation)	-40 °C ... 125 °C

### Mounting

Assembly note	Not for HC-B...EMC housings The guide pins of the protective cover must be removed when using coding sockets, pins, and bolts.
---------------	---

# HC-B 16-SD-MQT/FS-AL - Protective cover




1584554

<https://www.phoenixcontact.com/us/products/1584554>

## Drawings

Dimensional drawing



Dimensional drawing

# HC-B 16-SD-MQT/FS-AL - Protective cover



1584554

<https://www.phoenixcontact.com/us/products/1584554>

## Classifications

### ECLASS

ECLASS-13.0	27440208
ECLASS-15.0	27440208

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# HC-B 16-SD-MQT/FS-AL - Protective cover



1584554

<https://www.phoenixcontact.com/us/products/1584554>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)