

HC-B 10-AML-A - Housing

1586170

<https://www.phoenixcontact.com/us/products/1586170>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON B10 panel mounting base, with single locking latch made of sheet steel, height: 27 mm, with flat gasket

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1586170 |
| Packing unit | 10 pc |
| Minimum order quantity | 20 pc |
| Product key | AF7AAC |
| GTIN | 4046356353274 |
| Weight per piece (including packing) | 126.38 g |
| Weight per piece (excluding packing) | 126.38 g |
| Country of origin | DE |

HC-B 10-AML-A - Housing

1586170

<https://www.phoenixcontact.com/us/products/1586170>



Technical data

Product properties

| | |
|--------------|----------------------------|
| Product type | Housing with locking latch |
|--------------|----------------------------|

Dimensions

Installation dimensions

| | |
|-------------------------------|-------|
| Width of the assembly cutout | 35 mm |
| Length of the assembly cutout | 65 mm |

Material specifications

| | |
|---------------|-----|
| Seal material | NBR |
| | CR |

Connection data

| | |
|-------------------|----------------------------------|
| Tightening torque | 1.5 Nm ... 2 Nm (Mounting screw) |
|-------------------|----------------------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|----------------------|------|
| Degree of protection | IP65 |
|----------------------|------|


HC-B 10-AML-A - Housing

1586170

<https://www.phoenixcontact.com/us/products/1586170>



Drawings



Mounting cutout

HC-B 10-AML-A - Housing

1586170

<https://www.phoenixcontact.com/us/products/1586170>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440202 |
| ECLASS-15.0 | 27440202 |

HC-B 10-AML-A - Housing



1586170

<https://www.phoenixcontact.com/us/products/1586170>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com