

# BC-04S2NU2HH00 - Device connector rear mounting



1590093

<https://www.phoenixcontact.com/us/products/1590093>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 4-position, Socket, straight, M12, Wave soldering, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

Item number	1590093
Packing unit	100 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Sales key	AC10
Product key	ABQEQA
GTIN	4046356185455
Weight per piece (including packing)	19.07 g
Weight per piece (excluding packing)	17.554 g
Customs tariff number	85366990
Country of origin	DE

## Technical data

### Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

### Mounting

Mounting type	Rear mounting
---------------	---------------

### Product properties

Product type	Circular connectors (device side)
Number of positions	4
Thread type	M12

### Material specifications

Material Housing	CuZn
Material Housing surface	Ni
Material Contact carrier	PA 6T/66
Material Contact	CuZn
Material Contact surface	Au
Material Seal	FPM
Flammability rating according to UL 94	V0

### Connection data

#### Conductor connection

Connection method	Wave soldering
Contact connection type	Socket

### Connector

#### Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP67
UL Type Rating	Type 4 (indoor use only)

1590093

<https://www.phoenixcontact.com/us/products/1590093>

## Classifications

### ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

### ETIM

ETIM 10.0	EC003568
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1590093

<https://www.phoenixcontact.com/us/products/1590093>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	6b8cc60f-1636-40d0-a2f0-4175bb39f7b3

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)