

NC-06S1N8AMSEK - Coupler connector



1592044

<https://www.phoenixcontact.com/us/products/1592044>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Coupler connector, series: RC, straight plastic-sheathed, shielded: yes, Screw locking mechanism. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1592044
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRIEA
GTIN	4046356190350
Weight per piece (including packing)	45.08 g
Weight per piece (excluding packing)	41.428 g
Country of origin	DE

NC-06S1N8AMSEK - Coupler connector



1592044

<https://www.phoenixcontact.com/us/products/1592044>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Housing

Type	Coupling housing
Thread type	M23
Design	straight plastic-sheathed
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Seal)	FPM (O-ring)
Degree of protection (plugged in)	IP67

Environmental and real-life conditions

Ambient conditions

Permissible humidity (storage/transport)	50 % ... 65 %
--	---------------

NC-06S1N8AMSEK - Coupler connector

1592044

<https://www.phoenixcontact.com/us/products/1592044>



Drawings

NC-06S1N8AMSEK - Coupler connector



1592044

<https://www.phoenixcontact.com/us/products/1592044>

Classifications

ECLASS

ECLASS-13.0	27440312
ECLASS-15.0	27440312

ETIM

ETIM 10.0	EC002641
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

NC-06S1N8AMSEK - Coupler connector



1592044

<https://www.phoenixcontact.com/us/products/1592044>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	13531529-eacf-4a56-8fa7-812209b900f2

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com