

RC-000000090EM - Coupler connector



1592744

<https://www.phoenixcontact.com/us/products/1592744>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Coupler connector, series: RC, straight, shielded: yes, Screw locking mechanism, cable diameter range: 3 mm ... 10.5 mm Alternative products: 1554111

Commercial data

Item number	1592744
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFI
GTIN	4046356192477
Weight per piece (including packing)	65.774 g
Weight per piece (excluding packing)	65.774 g
Country of origin	DE

RC-000000090EM - Coupler connector



1592744

<https://www.phoenixcontact.com/us/products/1592744>

Technical data

Product properties

Product type	Circular connector housing
--------------	----------------------------

Connector

Housing

Type	Coupling housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP67

Seal

External cable diameter	3 mm ... 10.5 mm
Seal material	NBR

RC-000000090EM - Coupler connector



1592744

<https://www.phoenixcontact.com/us/products/1592744>

Classifications

ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

ETIM

ETIM 9.0	EC003556
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-000000090EM - Coupler connector



1592744

<https://www.phoenixcontact.com/us/products/1592744>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	1c8dff36-f79d-4c78-8e69-f05b1746d73b

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com