

RC-0000000K0FZ - Housing for circular connector



1592865

<https://www.phoenixcontact.com/us/products/1592865>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing for circular connector, series: RC, straight plastic-sheathed, Screw locking mechanism, M23, shielded: yes, this item is expected to be lead-free from Q1 2027 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1592865
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAFE
GTIN	4046356193122
Weight per piece (including packing)	35.51 g
Weight per piece (excluding packing)	30.89 g
Customs tariff number	85366990
Country of origin	DE

RC-0000000K0FZ - Housing for circular connector



1592865

<https://www.phoenixcontact.com/us/products/1592865>

Technical data

Product properties

Product type	Circular connector housing
Series	RC
Application	Signal
Shielded	yes
Thread type	M23

Material specifications

Material Housing	GD-Zn
Material Rotating parts	CuZn
Seal material	FPM or NBR or EPDM
Gasket and O-ring material	FPM

Connector

Type	straight plastic-sheathed
------	---------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

RC-0000000K0FZ - Housing for circular connector



1592865

<https://www.phoenixcontact.com/us/products/1592865>

Classifications

ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

ETIM

ETIM 10.0	EC003556
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

1592865

<https://www.phoenixcontact.com/us/products/1592865>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	05cc6403-d7f1-47ec-a67b-42acde93a545

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com