

# RC-0000000Z500 - Sleeve housing for cable connector



1593049

<https://www.phoenixcontact.com/us/products/1593049>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Sleeve housing for cable connector, series: RC, angled, Screw locking mechanism, M23, shielded: no, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1240318



## Commercial data

Item number	1593049
Packing unit	8 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFE
GTIN	4046356194013
Weight per piece (including packing)	148.15 g
Weight per piece (excluding packing)	139.28 g
Country of origin	DE

1593049

<https://www.phoenixcontact.com/us/products/1593049>

## Technical data

### Notes

Order information:	Order contact inserts and cable clamping separately
--------------------	---

### Product properties

Product type	Sleeve housings
Series	RC
Application	Signal
Type of the screw connection	IP65 screw
Shielded	no
Thread type	M23

### Material specifications

Housing material	Metal
------------------	-------

### Connector

Type	angled
------	--------

### Mechanical properties

#### Mechanical data

Type of the screw connection	IP65 screw
------------------------------	------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

# RC-0000000Z500 - Sleeve housing for cable connector



1593049

<https://www.phoenixcontact.com/us/products/1593049>

## Drawings

Dimensional drawing



Dimensional drawing

# RC-0000000Z500 - Sleeve housing for cable connector



1593049

<https://www.phoenixcontact.com/us/products/1593049>

## Classifications

### ECLASS

ECLASS-13.0

27440224

### UNSPSC

UNSPSC 21.0

39121400

1593049

<https://www.phoenixcontact.com/us/products/1593049>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	087ae559-cde6-4933-9c30-bdfed25068ff

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
 586 Fulling Mill Road  
 Middletown, PA 17057, United States  
 (+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)